

# Product data sheet

## Characteristics

# CLITPWL1

Clipsal - Lighting, 6W LED Wall Light, 4000K, IP54, Single Silver Body



## Main

Range	Clipsal
Product name	TPWL Series
Product or component type	Wall light
Device application	Lighting

## Complementary

Type of installation	Outdoor
Total system power	6 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R <sub>a</sub> =70
Luminous flux	330 lm
Bulb lifespan	36000 h
Colour temperature	4000 K
Colour	Body: silver
Device mounting	Wall mounted
Mounting mode	Surface mounted
Electrical insulation class	Class I
Shape	Rectangular
Length	157 mm
Width	70 mm
Depth	108 mm
Net weight	0.6 kg
Targeted country	Australia New Zealand

## Environment




IP degree of protection	IP54
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.5 cm
Package 1 Width	8.5 cm
Package 1 Length	11.5 cm
Package 1 Weight	649.75 g

Unit Type of Package 2	CAR
Number of Units in Package 2	8
Package 2 Height	18.8 cm
Package 2 Width	24.4 cm
Package 2 Length	34.0 cm
Package 2 Weight	5.502 kg

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>