

Product data sheet

Characteristics

DCDAL31M

DALI - 30 mechanism switch



Main

Range	DALI Control
Product or component type	Switch
Device application	Control

Complementary

Device presentation	Complete product
Number of channels	20
[Ue] rated operational voltage	9.5...22.5 V DC
Maximum [Ie] rated operational current	5 mA
Connections - terminals	2.5 mm ² screw connection
Wiring mode	2 wires
Local signalling	LED for status configurable
Ambient air temperature for operation	0...45 °C
Standards	AS/NZS CISPR15 EN 61347-2-11 EN 61547 EN 55015 AS/NZS 61347-2-11
Thickness	10 mm
Height	23 mm
Width	23 mm
Depth	41 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	6 cm
Package 1 Length	10 cm
Package 1 Weight	0.001 g

Offer Sustainability

EU RoHS Directive	Not compliant
-------------------	---------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.