


Product data sheet

Characteristics

DCDALCIP250-2

DALIcontrol Lighting Control System, Din-Mount Power Supply & Serial Interface, Two Dali lines



Main

Range	DALI Control
Product brand	Clipsal
Product or component type	Dual power supply and serial interface
Device application	Communication Power supply

Complementary

Output current	≤ 235 mA
[Us] rated supply voltage	110 V AC 50 Hz 240 V AC 60 Hz
Output current	≤ 235 mA line
Supply circuit type	AC
Number of lines feed	2
Number of modules	4
Local signalling	LED
Mounting support	DIN rail

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	7.8 cm
Package 1 Length	9.6 cm
Package 1 Weight	208.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes