

Product data sheet

Characteristics

E2315FBP

Switchboard Metal Back Plate, MAX9, Type 2, 3 Row



Main

Range	MAX9
Product or component type	Back plate

Complementary

Height	600 mm
Number of horizontal rows	3
Width	252 mm
Enclosure material	Galvanized steel
Depth	1.6 mm
Provided equipment	(1) plate (4) screws Earthing wire

Environment



Standards	AS/NZS 3000
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.3 cm
Package 1 Width	25.25 cm
Package 1 Length	60.0 cm
Package 1 Weight	2.076 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	7-year
----------	--------