

## Product data sheet

### Characteristics

# EVA1HPC1

EVlink Home, Anti-tripping module, 1P,  
maximum current allowed to charging station  
manually setting from 16A to 50A



### Main

Range	EVlink
Product or component type	Load-shedder
Material	Plastic

### Complementary

Range compatibility	EVlink EVlink Home
Condition of use	Indoor
Mounting support	35 mm DIN rail
Setting of maximum current provided to charging station	Manual
Possible maximum current provided to charging station	16 A 20 A 25 A 32 A 40 A 50 A
[Us] rated supply voltage	220...230 V AC 50/60 Hz +/- 10 %
Power consumption in W	4 W
Connectivity to devices	PLC
Local signalling	1 green LED, function: control process 1 red LED, function: fault indication 1 green LED, function: embedded communication status
Standards	EN 61010-1:2010 EN 61326-1:2013
Quantity per set	Set of 1
Height	70 mm
Width	93 mm
Depth	69 mm
Net weight	196 g
Colour	White

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

Operating altitude	0...2000 m
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	5...95 %
Overvoltage category	III
Pollution degree	2

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	10.100 cm
Package 1 Length	17.600 cm
Package 1 Weight	515.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	20
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	10.540 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>