

Product data sheet

Characteristics

EVF2S7P44

EVlink PARKING Floor Standing 7KW 2xT2 with Shutter EV CHARGING STATION



Main

Range	EVlink
Product name	EVlink parking
Product or component type	Charging station
Device short name	EVF2
Poles description	1P + N for control circuit 1P + N for power circuit
Mounting mode	Floor-standing
Offer type	Standard
Rated supply voltage	230 V AC 50/60 Hz power circuit 220...240 V AC 50/60 Hz control circuit
Earthing system	TT IT TN
Socket-outlet number	2
Socket-outlet type	Right: T2 with shutter / silver plated contacts Left: T2 with shutter / silver plated contacts
Maximum supply current	32 A for T2 with shutter
Max power	7 kW for T2 with shutter

Complementary

Control type	2 red push-button, function: stop 2 green illuminated push-button, function: start/unlock flap
Local signalling	On charge: 2 LED (green) (flashing) on side Available: 2 LED (green) on front Reserved: 2 LED (orange) on front Not operational: 2 LED (red) on front
Communication port protocol	OCP1.6
Configuration /Architecture	Clustered architecture Standalone
Operation and maintenance	Diagnosis capabilities Circuit breaker status User privilege configuration Load management Postponed charge Charge detail records
Web server	Embedded
Ethernet service	Configuration via web server
Standards	IEC 61851-22 IEC 61851-1
Product certifications	ZE Ready[RETURN]EV Ready[RETURN]CB[RETURN]CE
Height	1146 mm
Width	413 mm
Depth	220 mm
Net weight	50 kg
Colour	Front: white (RAL 9003) Side: grey (RAL 7016)

Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK10 socket-outlet conforming to IEC 61851-22
Ambient air temperature for operation	-30...50 °C conforming to IEC 61851-22
Ambient air temperature for storage	-40...80 °C
Operating altitude	0...2000 m conforming to IEC 61851-22
Relative humidity	0...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	38.0 cm
Package 1 Width	45.0 cm
Package 1 Length	128.0 cm
Package 1 Weight	58.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information