

Product data sheet

Characteristics

EVH2S3P0CK

EVlink Wallbox - 3.7 kW - T2 attached cable - charging station



Main

Range	EVlink
Product name	EVlink Wallbox
Product or component type	Charging station
Device short name	EVH2
Poles description	1P + N
Mounting mode	Wall-mounted
Offer type	Standard
Max power	3.7 kW 16 A
Number of charge point	1
Connection to the vehicle	Attached cable T2 4 m
Access control system	Key

Complementary

Rated supply voltage	220...240 V AC 50/60 Hz
Earthing system	TT TN
Number of inputs	1
Input type	Contact for power limitation Contact for delayed charging
Control type	1 white button, function: stop/restart Green button, function: cable unlocking
Local signalling	1 multi-colour LED, function: status indication
Height	480 mm
Width	330 mm
Depth	170 mm
Net weight	7.5 kg
Colour	White (RAL 9003) Grey (RAL 7016)
Standards	IEC 62196-2 IEC 61851-1 IEC 61851-22 IEC 62196-1
Product certifications	CE CB

Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	9.017 kg
Package 1 Height	25.5 cm
Package 1 width	39.8 cm
Package 1 Length	53.5 cm
Unit Type of Package 2	P06
Number of Units in Package 2	4
Package 2 Weight	44.568 kg
Package 2 Height	77 cm
Package 2 width	60 cm
Package 2 Length	80 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information