

## Product data sheet

### Characteristics

# EVP1CNS32121

## EVlink Charging cable 5m 32A 1-Phase T2-T1

### IEC EV accessory

#### Main

Range	EVlink
Product or component type	Charging cable
Accessory / separate part category	Cabling accessory
Network number of phases	Single phase
Poles description	1P + N
[In] rated current	32 A
[Us] rated supply voltage	220...240 V AC 50/60 Hz
Socket number	2

#### Complementary

Connector type	T2 charging station end silver plated contacts T1 vehicle end silver plated contacts
Range compatibility	EVlink EVlink parking EVF1 charging station EVlink EVlink parking EVW1 charging station EVlink EVlink parking EVF2 charging station EVlink EVlink parking EVW2 charging station EVlink EVlink Smart Wallbox EVB1 charging station EVlink EVlink Wallbox EVH2 charging station
Standards	IEC 62196-1 IEC 62196-2
Product certifications	CE
Length	5 m
Net weight	2.4 kg

#### Environment

IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	36 cm
Package 1 Length	44 cm
Package 1 Weight	2.425 kg
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm

Package 2 Weight	10.597 kg
Unit Type of Package 3	P06
Number of Units in Package 3	16
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	48.5 kg

### Offer Sustainability

SCIP Number	8e1f5fe5-e420-494e-86aa-24ecfc5c83fe
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>