

Product data sheet

Characteristics

L18

Clipsal MAX4, Mini Neutral link 100 A 500 V 18 hole with cover Black



Main

Range	MAX9
Product brand	Clipsal
Range of product	Blue Point
Product or component type	Neutral link

Complementary

Cable cross section	16 mm ²
[In] rated current	100 A
[Ue] rated operational voltage	500 V
Connector type	Screw terminals
Number of poles	1
Number of mounting holes	18
Height	86 mm
Width	57 mm
Depth	40 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	5.6 cm
Package 1 Length	8.4 cm
Package 1 Weight	139 g
Unit Type of Package 2	CAR
Number of Units in Package 2	60
Package 2 Height	25 cm
Package 2 Width	21.4 cm
Package 2 Length	33.8 cm
Package 2 Weight	9.165 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	No need of specific recycling operations