

Product data sheet

Characteristics

L5102D10

C-Bus Control and Management System, Dimmer Module, 2 Channel, Leading Edge, 250V, 10A



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Load type	Inductive

Complementary

Power consumption in VA	2400 VA
Network frequency	47...63 Hz
Nominal output power	2300 W
Local signalling	LED
Number of channels	2
Mounting support	Wall
Size	Base: 240 x 202 x 75 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	23.4 cm
Package 1 Length	24.5 cm
Package 1 Weight	4.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

