

Product data sheet

Characteristics

L5104D5

Dimmer Module, C-Bus Control and Management System, 4 Channel, Leading Edge, 250V, 5A



Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Dimmer
Device application	Control
Device presentation	Basic element
Load type	Inductive

Complementary

Power consumption in VA	1200 VA
Network frequency	47...63 Hz
Nominal output power	1150 W
Local signalling	LED
Number of channels	4
Mounting support	Wall
Size	Base: 240 x 202 x 75 mm

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.606 cm
Package 1 Width	26.411 cm
Package 1 Length	24.825 cm
Package 1 Weight	2.441 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	25.6 cm
Package 2 Width	34.9 cm
Package 2 Length	40.2 cm
Package 2 Weight	10.36 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information