

## Product data sheet

### Characteristics

# L5501RFCP

## Relay, C-Bus, DIN Rail Mounted, Fan Control, 240V AC, 1 Channel, 1.5A, Without C-Bus Power Supply



### Main

Range of product	C-Bus
Product brand	Clipsal
Range	C-Bus
Product or component type	Relay
Device application	Fan speed controller

### Complementary

Rated voltage	100...250 V AC 50/60 Hz
Local signalling	LED
Connector type	Screw terminals
[Us] rated supply voltage	15...36 V DC
Nominal output power	350 W
Number of modules	3
Number of channels	1
Width	55 mm
Height	93 mm
Depth	65 mm
Device mounting	DIN rail

### Environment

IP degree of protection	IP20
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	11.5 cm
Package 1 Length	15.5 cm
Package 1 Weight	273.0 g
Unit Type of Package 2	PAL
Number of Units in Package 2	240
Package 2 Height	103.0 cm
Package 2 Width	66.0 cm
Package 2 Length	67.5 cm
Package 2 Weight	91.6 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	8
Package 3 Height	20.6 cm
Package 3 Width	22.5 cm
Package 3 Length	33.0 cm
Package 3 Weight	2.72 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins