

Product data sheet

Characteristics

ML2025I-WE

Twin Switch Socket Outlet, Medilec, 250V, 10A, 2 Gang, 1 Pole

Main

Range of product	Medilec ML2000 Moulded Series
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Indicator light
Installation Orientation	Horizontal
Material	Plastic
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Length	116 mm
Width	76 mm

Environment

Standards	AS/NZS 3112:approval number S/1/2025 AS/NZS 3112:approval number S/1/2015
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.5 cm
Package 1 Length	11.5 cm
Package 1 Weight	120 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes