

Product data sheet

Characteristics

NSYTBP342912

PC box, Thalassa, IP66 IK08 RAL7035
Int.H325W275D120 Ext.H341W291D128
opaque PC cover H20

Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	341 mm
Width	291 mm
Depth	128 mm
Internal height	325 mm
Internal width	275 mm
Internal depth	120 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035)
Standards	IEC 62208 UL 508 A
Product certifications	TÜV[RETURN]UL
Electrical insulation class	Class II
Mounting location	Outdoor (with canopy or shelter and anticondensation valve)
Net weight	1.16 kg

Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	14.000 cm
Package 1 Width	30.000 cm
Package 1 Length	35.500 cm
Package 1 Weight	1.570 kg

Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	40.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	7.058 kg
Unit Type of Package 3	P12
Number of Units in Package 3	48
Package 3 Height	136.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	102.500 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	No

Contractual warranty

Warranty	18 months
----------	-----------