

## Product data sheet

### Characteristics

# NSYTBP885

PC box IP66 IK08 RAL7035 Int.H80W80D65  
Ext.H89W89D51 opaque PC cover H10



### Main

Range	Thalassa
Product name	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	89 mm
Width	89 mm
Depth	54 mm
Internal height	80 mm
Internal width	80 mm
Internal depth	47 mm
Enclosure mounting	Wall mounted
Device composition	1 body 1 cover 4 cover screw
Quantity per set	Set of 5
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Metal screws
Lock type	Captive screw flat outside sealed area
Removable parts	Cover by captive screws

### Complementary

Material	Polycarbonate
Colour	Grey (RAL 7035)
Standards	UL 508 A IEC 62208
Product certifications	TÜV UL
Electrical insulation class	Class II
Mounting location	Outdoor (with canopy or shelter and anticondensation valve)
Net weight	0.108 kg

### Environment

IP degree of protection	IP66 conforming to NEMA 4.4X
IK degree of protection	IK08 conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	108.0 g
Package 1 Height	5.1 cm
Package 1 width	8.9 cm
Package 1 Length	8.9 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	160
Package 2 Weight	18.66 kg
Package 2 Height	41.0 cm
Package 2 width	60.0 cm
Package 2 Length	160.0 cm
Unit Type of Package 3	PAL
Number of Units in Package 3	4000
Package 3 Weight	481.5 kg
Package 3 Height	100.0 cm
Package 3 width	120.0 cm
Package 3 Length	4000.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------