

Product data sheet

Characteristics

P2032VA-WE

Prestige Series, Flush Switch, 2 Gang, 250VAC, 10A, Standard, Vertical



Main

Range of product	Prestige Series P2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

Complementary

[Ue] rated operational voltage	230/240 V
Number of poles	1
Installation Type	Flush
Number Of Switches	2
Local signalling	without
[Ue] rated operational voltage	230/240 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	2-way 1-way

Environment

Standards	AS/NZS 3133 AS/NZS 3100
-----------	----------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.7 cm
Package 1 Width	7.8 cm
Package 1 Length	12.7 cm
Package 1 Weight	54.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations