

## Product data sheet

### Characteristics

# PDL100MPIR

## Motion Sensor Module PDL - Passive Infrared - Indoor - LED indicator - 250 V



### Main

Range of product	PDL Sensors
Product or component type	Sensor
Colour tint	White Black
Load type	750 W incandescent 100 W fluorescent 400 W halogen 100 W motor
Quantity per set	Set of 10
Type of packing	Carton

### Complementary

Material	PC (polycarbonate)
Surface finish	Glossy Matt
[In] rated current	3 A
Rated voltage	230...250 V AC 50 Hz
Network number of phases	1 phase
Mounting location	Front of modular console
Installation direction	Horizontal Vertical
Width	23 mm
Height	23 mm

### Environment

IP degree of protection	IP55
Ambient air temperature for operation	-10...50 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	38.0 g
Package 1 Height	2.5 cm
Package 1 width	8 cm
Package 1 Length	10 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

---