

Product data sheet

Characteristics

PDL100MPIR

Motion Sensor Module PDL - Passive Infrared - Indoor - LED indicator - 250 V



Main

Range of product	PDL Sensors
Product or component type	Sensor
Colour tint	White Black
Load type	750 W incandescent 100 W fluorescent 400 W halogen 100 W motor
Quantity per set	Set of 10
Type of packing	Carton

Complementary

Material	PC (polycarbonate)
Surface finish	Glossy Matt
[In] rated current	3 A
Rated voltage	230...250 V AC 50 Hz
Network number of phases	1 phase
Mounting location	Front of modular console
Installation direction	Horizontal Vertical
Width	23 mm
Height	23 mm

Environment

IP degree of protection	IP55
Ambient air temperature for operation	-10...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	8 cm
Package 1 Length	10 cm
Package 1 Weight	38 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	76 cm
Package 2 Width	118 cm
Package 2 Length	194 cm
Package 2 Weight	0.424 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information