

# Product data sheet

## Characteristics

# PDL151

## 10-Way 60 deg. Maximum Connector Strip; 32A, 500V, Orange



### Main

Range of product	PDL General Accessories
Product or component type	Connector block
Colour tint	Orange
Quantity per set	Set of 20
Type of packing	Bag

### Complementary

Material	PE (polyethylene)
Surface finish	Glossy
Installation direction	Vertical Horizontal
[In] rated current	32 A
Rated voltage	500 V
Operating angle	60 °
Connections - terminals	Screw terminals
Height	15.6 mm
Width	18.4 mm
Length	96.2 mm
Number of ways	10 ways

### Environment

Ambient air temperature for operation	-10...40 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.56 cm
Package 1 Width	1.84 cm
Package 1 Length	9.62 cm
Package 1 Weight	36.21 g

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Circularity Profile	No need of specific recycling operations