

Product data sheet

Characteristics

PDL29SWH

Skirt; For Batten Lamp Holder, White



Main

Range of product	PDL Lighting and Accessories
Product or component type	Batten holder
Colour tint	White
Load type	150 W lamp
Quantity per set	Set of 20
Type of packing	Carton

Complementary

Material	Thermoplastic
Surface finish	Glossy
[Ue] rated operational voltage	230/240 V AC 50 Hz
Network number of phases	1 phase
Thread type	BSW 18TPI
Diameter	Outside: 39.4 mm Inside: 37.4 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	4 cm
Package 1 Length	4 cm
Package 1 Weight	12 g

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations