

## Product data sheet

### Characteristics

# PDL342USB2AC-VW

PDL Iconic, 2 USB Charger, type A, type C,  
Vivid White



### Main

Range	PDL Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	2 USB type A 5 V DC, maximum load current: 2.4 A USB type C, maximum load current: 3 A
Maximum load current with 2 outputs used simultaneously	3.1 A 3.1 A

### Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	Vivid white (VW)
Surface finish	Glossy
Fixing mode	By clips
Type of packing	Box
Quantity per set	1
Sale per indivisible quantity	1
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	5...90 %
Protection type	Short time short-circuit protection
Number of terminals	1 with cable end
Height	48 mm
Width	27 mm
Depth	59 mm
Embedding depth	55 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.