

Product data sheet

Characteristics

PDL342USB2AC-VW

Iconic, Module Dual USB Charger, Type A+C, 15W, 300 Series, Vivid White



Main

Range	PDL Iconic
Product or component type	USB charger
[Ue] rated operational voltage	220/240 V AC 50 Hz
Integrated connection type	2 USB type A 5 V DC, maximum load current: 2.4 A USB type C, maximum load current: 3 A
Maximum load current with 2 outputs used simultaneously	3.1 A 3.1 A




Complementary

Device mounting	Flush
Device presentation	Mechanism
Colour tint	Vivid white (VW)
Surface finish	Glossy
Fixing mode	By clips
Type of packing	Box
Quantity per set	1
Sale per indivisible quantity	1
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	5...90 %
Protection type	Short time short-circuit protection
Number of terminals	1 with cable end
Height	48 mm
Width	59 mm
Depth	59 mm
Embedding depth	55 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	6.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	100 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes