

Product data sheet

Characteristics

PDL348PB10TMBT-VW

PDL Iconic 10A 240V pushbutton timer mechanism, 3 wire with ControlLink



Main

Range	PDL Iconic
Product or component type	Timer
Device presentation	Mechanism

Complementary

Device mounting	Flush
Actuator	Push-button
Fixing mode	Clip-in
Colour tint	Vivid white
Surface finish	Matt
Type of packing	Box
Sale per indivisible quantity	1
Time delay	1...86400 s (24 h) adjustable
Remote control type	Push-button Wiser room application
[Ue] rated operational voltage	240 V AC 50 Hz
Load type	LED lighting 10 A Incandescent lamp 10 A Low voltage halogen lamp with iron core transformer 10 A Low voltage halogen lamp with electronic transformer 10 A Fluorescent lamp 10 A Compact fluorescent lamp 10 A Resistive 15 A
Power range	> 0 W
Derating factor	1 devices 10 A without derating 2 devices 7.5 A with derating factor 3 devices 6.5 A with derating factor
Operating distance	30 m
Control signal type	ControlLink
Connections - terminals	Screw terminals
Number of terminals	4
Wiring configuration	3 wires with neutral
Screwdriver shape	Square drive no 1 (SQ1) Philips
Local signalling	LED indicator (warm white)
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	24 mm
Width	48 mm

Depth	55 mm
Embedding depth	52 mm
Standards	AS/NZS 60669.2.1

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	0...90 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	6.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	85 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information