



Main

Range	PDL Iconic
Product or component type	Timer
Device presentation	Mechanism

Complementary

Device mounting	Flush
Actuator	Push-button
Fixing mode	Clip-in
Colour tint	Vivid white
Surface finish	Matt
Type of packing	Box
Sale per indivisible quantity	1
Remote control type	Push-button
[Ue] rated operational voltage	240 V AC 50 Hz
Operating distance	30 m
Control signal type	Controllink
Connections - terminals	Screw terminals
Number of terminals	2
Wiring configuration	2-wire
Screwdriver shape	Square drive no 1 (SQ1) Philips
Material	PC (UL94 V-2): top PC MAS056 (UL94 V-2): bottom
Height	22 mm
Width	22 mm
Depth	40 mm
Embedding depth	38 mm

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	0...90 %

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information