

Product data sheet

Characteristics

PDL356PBSSL-VW

ControlLink module, Iconic, with LED indicator, 3-wire, 220–240 V, Vivid white



Main

Product brand	PDL
Range	PDL Iconic
Aesthetic name	Iconic
Product or component type	Remote control auxiliary

Complementary

Device presentation	Mechanism
Device application	Light control
[Ue] rated operational voltage	220...240 V AC 50 Hz
Number of FUNCTION keys	1
Local signalling	Programmable: 1 LED (green/red)
Signalling function	Programming indication Light ON when switch is actuated Locator
Number of outputs	1
Control type	Local control dimming up/down control Local control on/off switching
Communication network type	Wired ControlLink
Connected auxiliaries	1 Wiser dimmer, distance : 50 m
Provided equipment	User manual
Wiring configuration	With neutral
Connections - terminals	Screw terminal
Clamping connection capacity	1.5...2.5 mm ² for solid cable(s) 1.5...2.5 mm ² for solid stranded cable(s)
Shape of screw head	Pozidriv No 1 and combi
Tightening torque	0.5 N.m
Material	PC (polycarbonate) GF10 FR: casing Metal: terminals
Mounting support	Wall
Device mounting	Flush
Fixing mode	Clip-in
Type of installation	Indoor installation
Quantity per set	1 carton
Embedding depth	41 mm
Depth	41 mm
Width	22 mm
Height	22 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	5...40 °C
Ambient air temperature for storage	5...40 °C
IP degree of protection	IP20
Standards	AS/NZS CISPR 15 AS/NZS 60669.2.1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information