

## Product data sheet

### Characteristics

# PDL381-VW

## Switch Iconic - Assembled - Vertical - 1-gang - 230/240V - 20 A / 10 AX - Vivid White



### Main

Range of product	PDL Iconic
Product or component type	Switch
Device application	Lighting
Device presentation	Complete switch
Provided equipment	Switch Screws Skin Grid plate
Colour	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20
Sale per indivisible quantity	1
Motor M-rating AS3133	M80
Load type	Fluorescent 10 A LEDi lamp 100 W Inductive Light Fluorescent lamp

### Complementary

Device mounting	Flush
Switch function	1/2-way
[Ue] rated operational voltage	230/240 V
Number of gangs	1 gang vertical 84 mm
Number of rocker	1
Actuator	Rocker
Fixing mode	By screws
Surface finish	Matt
Surface treatment	Untreated
Rated current	20 A/16 AX at 230/240 V AC 50 Hz
Electrical durability	20000 cycles conforming to AS/NZS 60669
Connections - terminals	4 screw terminals
Screwdriver shape	Philips No 2 Square drive no 1 (SQ1)
Clamping connection capacity	1.5 mm <sup>2</sup> for stranded cable(s) 1.5 mm <sup>2</sup> for flexible cable(s) 1.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	10 mm
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin PC (polycarbonate): grid plate PP (polypropylene): flaps PC (polycarbonate): housing PA66: housing POM (polyoxymethylene): locking bar
Height	120 mm
Width	78 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Depth	39 mm
Net weight	0.78 kg

## Environment

Dielectric strength	20000 V
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	10...95 %
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	7.8 cm
Package 1 Length	7.5 cm
Package 1 Weight	75 g

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>