

Product data sheet

Characteristics

PDL381VWP-VW

Waterproof Switch, Iconic, 1-Gang 20A IP44 Vertical



Main

Range of product	PDL Iconic
Product or component type	Switch
Device application	Lighting
Device presentation	Complete switch
Provided equipment	IP44 gridplate and switch Screws Skin
Colour	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20
Sale per indivisible quantity	1
Motor M-rating AS3133	M80
Load type	Inductive Light Fluorescent lamp

Complementary

Device mounting	Flush
Switch function	1/2-way
[Ue] rated operational voltage	230/240 V
Number of gangs	1 gang vertical 84 mm
Number of rocker	1
Actuator	Rocker
Fixing mode	By screws
Surface finish	Matt
Surface treatment	Untreated
Rated current	20 A/16 AX at 230/240 V AC 50 Hz
Electrical durability	20000 cycles conforming to AS/NZS 60669
Connections - terminals	4 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Phillips No 2
Clamping connection capacity	1.5 mm ² for stranded cable(s) 1.5 mm ² for flexible cable(s) 1.5 mm ² for rigid cable(s)
Wire stripping length	10 mm
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin PC (polycarbonate): grid plate PP (polypropylene): flaps PC (polycarbonate): housing PA66: housing POM (polyoxymethylene): locking bar TPE (thermoplastic elastomer): switch seal PC (polycarbonate): wall seal TPE (thermoplastic elastomer): wall seal
Height	124 mm
Width	82 mm

Depth	40 mm
Product weight	0.098 kg

Environment

Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	10...95 %
Product certifications	RCM
IP degree of protection	IP44

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	7.8 cm
Package 1 Length	8 cm
Package 1 Weight	80 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations