

Product data sheet

Characteristics

PDL383GM10

Grid plate Mechanical assembly, Iconic, Vertical, 10AX 250V AC, 3 gang



Main

Range of product	Iconic
Range of product	Iconic
Product or component type	Grid plate
Device presentation	Mechanism with fixing frame
Load type	Fluorescent 10 A LEDi lamp 100 W

Complementary

Device mounting	Flush
Number of gangs	3 gangs
Range compatibility	Iconic
Rated current	10 AX at 250 V AC
Local signalling	Without light indicator

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.1 cm
Package 1 Length	11.5 cm
Package 1 Weight	90.0 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.