

## Product data sheet

### Characteristics

# PDL383L-VW

Iconic - 3gang vert switch assembly with white LED 20A/16AX 250V vivid white

### Main

Range of product	PDL Iconic
Product or component type	Switch
Device application	Lighting
Device presentation	Complete switch
Provided equipment	Skin Grid plate Switch LED Screws
Colour	Vivid white (VW)
Type of packing	Polybag
Quantity per set	Set of 20
Sale per indivisible quantity	1
Motor M-rating AS3133	M80
Load type	Fluorescent 10 A LEDi lamp 100 W Inductive Light Fluorescent lamp
Light source	LED 60 mW

### Complementary

Device mounting	Flush
Switch function	1/2-way
Number of gangs	3 gangs vertical 84 mm
Number of rocker	3
Actuator	Rocker
Fixing mode	By screws
Surface finish	Matt
Surface treatment	Untreated
Rated current	20 A/16 AX at 250 V AC 50 Hz
Electrical durability	20000 cycles conforming to AS/NZS 60669
Connections - terminals	4 screw terminals
Screwdriver shape	Square drive no 1 (SQ1) Phillips No 2
Clamping connection capacity	1.5 mm <sup>2</sup> for stranded cable(s) 1.5 mm <sup>2</sup> for flexible cable(s) 1.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	10 mm
Local signalling	LED warm white optional LED warm white for locator LED warm white for indicator
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin PC (polycarbonate): grid plate PP (polypropylene): flaps PC (polycarbonate): housing PA66: housing POM (polyoxymethylene): locking bar

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Height	120 mm
Width	78 mm
Depth	39 mm
Net weight	0.108 kg

## Environment

Dielectric strength	20000 V
Ambient air temperature for operation	0...45 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	10...95 %
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.3 cm
Package 1 Width	7.8 cm
Package 1 Length	10.9 cm
Package 1 Weight	109.37 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	33.5 cm
Package 2 Width	26.1 cm
Package 2 Length	33.5 cm
Package 2 Weight	6676.7 g
Unit Type of Package 3	PAL
Number of Units in Package 3	900
Package 3 Height	95 cm
Package 3 Width	100 cm
Package 3 Length	120 cm
Package 3 Weight	98.1 kg

## Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>