

## Product data sheet

### Characteristics

# PDL395RCD30-VW

Iconic, Double Switched Socket RCD, 30mA  
Horizontal 10A, Vivid White



### Main

Range	PDL Iconic
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

### Complementary

Device mounting	Flush
Number of power socket outlets	2
Number of rocker	2
Outlet standard description	With earthing contact
Outlet standard deviation	Australian/New Zealand
Ground lug position	Straight 180° position
Device composition	1 residual current device (RCD) 30 mA
Fixing mode	By screw
Installation direction	Horizontal
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 4
Sale per indivisible quantity	1
Electrical durability	12000 cycles
Screwdriver shape	Square drive no 1 (SQ1) Philips No 2
Clamping connection capacity	1 x 2.5...4 x 2.5 mm <sup>2</sup> for stranded cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for flexible cable(s) 1 x 2.5...4 x 2.5 mm <sup>2</sup> for rigid cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): skin ABS (acrylonitrile butadiene-styrene): skin PC (polycarbonate): fixing frame PP (polypropylene): flaps POM (polyoxymethylene): shutter
Height	78 mm
Width	120 mm
Depth	42 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned above. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.


## Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112 AS/NZS 3190
Product certifications	RCM

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.2 cm
Package 1 Width	7.8 cm
Package 1 Length	11 cm
Package 1 Weight	110 g

## Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>