

Product data sheet

Characteristics

PDL395USBAC-VW

PDL Iconic, switched socket, 2 switch & 2 socket, USB, horiz, 10 A, Vivid White



Main

Range	PDL Iconic
Product or component type	Switched socket
Device presentation	Complete product
Outlet poles configuration	2P + E with shutter
Outlet standard	Australian

Complementary

Device mounting	Flush
Number of power socket outlets	2
Number of rocker	2
Range compatibility	PDL Iconic
Outlet standard description	With earthing contact
Outlet standard	Australian/New Zealand
Ground lug position	Straight 180° position
Device composition	2 USB charger
Fixing mode	By screw
Installation direction	Horizontal
Colour	Vivid white (VW)
Surface finish	Matt
Type of packing	Polybag
Quantity per set	Set of 10
Sale per indivisible quantity	1
Connections - terminals	3 screw terminals
Screwdriver shape	Square drive no 1 (SQ1)
Clamping connection capacity	1 x 2.5...4 x 2.5 mm ² for stranded cable(s)
Wire stripping length	16 mm
Material	PC (polycarbonate): skin
Height	120 mm
Width	78 mm
Depth	44 mm

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	0...45 °C
Relative humidity	10...95 %
Standards	AS/NZS 3112

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------