

Product data sheet

Characteristics

PDL56AI310LEGY

Appliance Inlet, 10A, 250V, 3-Flat Pin, Grey



Main

Range of product	56 Series
Product or component type	Appliance inlet
Material	PC (polycarbonate)

Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	95 mm
Rated current	10 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Pin number	3
Device composition	Flat pin
Mounting mode	Surface mounted
Fixing center	84 x 84 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	1...6 mm ²
Quantity per set	Set of 4
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	9.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	305 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes