

# Product data sheet

## Characteristics

# PDL56AI416LE

## Appliance Inlet, 16A, 500V, 4-Round Pin, Grey

### Main

Range of product	56 Series
Product or component type	Appliance inlet
Material	PC (polycarbonate)



### Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Rated current	16 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	4
Device composition	Round pin
Mounting mode	Surface mounted
Fixing center	84 x 180 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	1...6 mm <sup>2</sup>
Quantity per set	Set of 2
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11 cm
Package 1 Width	9.5 cm
Package 1 Length	19 cm
Package 1 Weight	0.389 kg

### Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>