

## Product data sheet

### Characteristics

# PDL56AI440LE

## Appliance Inlet, 40A, 500V, 5-Round Pin, Grey



### Main

Range of product	56 Series
Product or component type	Appliance inlet
Material	PC (polycarbonate)

### Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Rated current	40 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	4
Device composition	Round pin
Mounting mode	Surface mounted
Fixing center	84 x 180 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	2.5...6 mm <sup>2</sup>
Quantity per set	Set of 2
Type of packing	Carton

### Packing Units

Package 1 Weight	496.000 g
------------------	-----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>