

Product data sheet

Characteristics

PDL56AI520LE

Appliance Inlet, 20A, 500V, 5-Round Pin, Grey



Main

Range of product	56 Series
Product or component type	Appliance inlet
Material	PC (polycarbonate)

Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Rated current	20 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	5
Device composition	Round pin
Mounting mode	Surface mounted
Fixing center	84 x 180 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	1...6 mm ²
Quantity per set	Set of 2
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	10.5 cm
Package 1 Length	19 cm
Package 1 Weight	403 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes