

# Product data sheet

## Characteristics

# PDL56AI550LE

## Appliance Inlet, 50A, 500V, 5-Round Pin, Grey



### Main

Range of product	56 Series
Product or component type	Appliance inlet
Material	PC (polycarbonate)

### Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Rated current	50 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	5
Device composition	Round pin
Mounting mode	Surface mounted
Fixing center	84 x 180 mm
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	4...16 mm <sup>2</sup>
Quantity per set	Set of 2
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	11 cm
Package 1 Length	19 cm
Package 1 Weight	468 g

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>