

# Product data sheet

## Characteristics

# PDL56C310RCD30LEGY

## RCD Protected Socket, 20A, 240V, 3-Flat Pin, 1-Gang, Grey

### Main

Range of product	56 Series™
Product or component type	Residual current device switch
Control type	Push-button

### Complementary

Material	Plastic
Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Pin number	3
Device composition	Flat pin
Mounting mode	Surface mounted
Fixing center	84 x 180 mm
IP degree of protection	IP66
Ambient air temperature for operation	-10...40 °C
Quantity per set	Set of 2
Type of packing	Carton

### Environment

Earth-leakage protection class	Class A
--------------------------------	---------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	9.5 cm
Package 1 Length	19 cm
Package 1 Weight	439 g

## Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Take-back	No