

PDL56C310RCD30LEGY

RCD Protected Socket, 20A, 240V, 3-Flat Pin, 1-Gang, Grey



Main

Range of product	56 Series™
Product or component type	Residual current device switch
Control type	Push-button

Complementary

Material	Plastic
Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	191 mm
Rated current	10 A
[Ue] rated operational voltage	230/240 V
Network frequency	50 Hz
Network number of phases	1 phase
Number of gangs	2 gangs
Pin number	3
Device composition	Flat pin
Mounting mode	Surface mounted
Fixing center	84 x 180 mm
IP degree of protection	IP66
Ambient air temperature for operation	-10...40 °C
Quantity per set	Set of 2
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.439 kg
Package 1 Height	6 cm
Package 1 width	9.5 cm
Package 1 Length	19 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile