

## Product data sheet

### Characteristics

# PDL56CB4LEGY

## DIN Rail Mounting Cover, 2-Gang, Grey



### Main

Range of product	56 Series™
Product or component type	Cover
Material	PC (polycarbonate)

### Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	198 mm
Depth	32 mm
Rated current	100 A
[Ue] rated operational voltage	415 V
[Ui] rated insulation voltage	1000 V
Number of gangs	2 gangs
Mounting mode	Surface mounted
IP degree of protection	IP66
Quantity per set	Set of 4
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.266 kg
Package 1 Height	50 mm
Package 1 width	95 mm
Package 1 Length	195 mm

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.