

Main

Range of product	56 Series™
Product or component type	Cover
Material	PC (polycarbonate)

Complementary

Colour tint	Grey
Surface finish	Gloss
Installation direction	Vertical
Width	95 mm
Height	198 mm
Depth	32 mm
Rated current	100 A
[Ue] rated operational voltage	415 V
[Ui] rated insulation voltage	1000 V
Number of gangs	2 gangs
Mounting mode	Surface mounted
IP degree of protection	IP66
Quantity per set	Set of 4
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	9.5 cm
Package 1 Length	19.5 cm
Package 1 Weight	302 g
Unit Type of Package 2	CAR
Number of Units in Package 2	24
Package 2 Height	205 cm
Package 2 Width	345 cm
Package 2 Length	450 cm
Package 2 Weight	8.36 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations