

Product data sheet

Characteristics

PDL56CR320

Cord Extension Socket, 20A, 250V, 3-Round Pin, Clear/Orange



Main

Range of product	56 Series™
Product or component type	Socket
Material	Plastic




Complementary

Colour tint	Orange
Surface finish	Gloss
Rated current	20 A
[Ue] rated operational voltage	250 V
Network frequency	50 Hz
Network number of phases	1 phase
Pin number	3
Device composition	Round pin
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm²
Quantity per set	Set of 4
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	17.3 cm
Package 1 Length	28.7 cm
Package 1 Weight	0.318 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes