

Product data sheet

Characteristics

PDL56CR416

56 Series, Cord Connector Extension Socket,
16A 500V 4-Round Pin IP66, Orange



Main

Range of product	56 Series™
Product or component type	Socket
Material	Plastic

Complementary

Colour tint	Orange
Surface finish	Gloss
Rated current	16 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	4
Device composition	Round pin
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm²
Quantity per set	Set of 4
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	8.0 cm
Package 1 Length	16.0 cm
Package 1 Weight	262 g

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes