

## Product data sheet

### Characteristics

# PDL56CRV520

## Cord Extension Socket, 20A, 500V, 5-Round Pin, Resistant Orange



### Main

Range of product	56 Series™
Product or component type	Socket
Material	PBT (polybutylene terephthalate)

### Complementary

Colour tint	Orange
Surface finish	Gloss
Rated current	20 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	5
Device composition	Round pin
IP degree of protection	IP66
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm <sup>2</sup>
Quantity per set	Set of 4
Type of packing	Carton

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.346 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.