

Product data sheet

Characteristics

PDL56CV440LEGY

Switched Socket, 40A, 500V, 4-Round Pin, 2-Gang, 3-Pole, Grey

Main

Range of product	56 Series
Product or component type	Switched socket
Control type	Rotary
Colour tint	Grey

Complementary

Material	Plastic
Surface finish	Gloss
Installation direction	Vertical
Dimension type	Cover only
Rated current	40 A
[Ue] rated operational voltage	500 V
Network frequency	50 Hz
Motor M-rating AS3133	M250
Network number of phases	3 phases
Number of gangs	2 gangs
Pin number	4
Device composition	Round pin
Number of poles	3
IP degree of protection	IP66
Fixing center	84 x 180 mm
Device mounting	Surface
Width	95 mm
Height	191 mm
Quantity per set	Set of 2
Type of packing	Carton

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	9.5 cm
Package 1 Length	19 cm
Package 1 Weight	664 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes