

Product data sheet

Characteristics

PDL56E4CG

56 Series, Enclosure, 4-Gang 2x25mm 4x32mm IP66, Chemical-Resistant Grey



Main

Product name	56 Series
Product or component type	Enclosure
Device short name	PDL56E4CG

Complementary

Material	PVC (polyvinyl chloride): housing
Device mounting	Surface
Mounting mode	Wall-mounted
Net weight	0.745 kg
Base dimension	198 x 198 mm
Height	198.0 mm
Width	198.0 mm
Depth	63.0 mm
Colour	Dark grey

Environment

Standards	AS 3100
IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	19.8 cm
Package 1 Length	19.8 cm
Package 1 Weight	0.82 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations