

Product data sheet

Characteristics

PDL56P310OR

Plug - Straight, 10A, 250V, 3-Flat Pin, Clear/
Orange



Main

Range	56 Series
Product or component type	Plug

Complementary

Rated current	10 A
[Ue] rated operational voltage	250 V
Material	Plastic
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	1 phase
Pin number	3
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm ²
Quantity per set	Set of 4
Type of packing	Carton

Environment

IP degree of protection	IP66
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.