

Product data sheet

Characteristics

PDL56P320FOR

56 Series, Plug Straight, 20A 250V 1-Phase 3-Flat Pin IP66, Orange



Main

Range	56 Series
Product or component type	Plug

Complementary

Rated current	20 A
[Ue] rated operational voltage	250 V
Material	Plastic
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	1 phase
Pin number	3
Ambient air temperature for operation	-40...55 °C
Cable cross section	10.6...12.5 mm ²
Quantity per set	Set of 4
Type of packing	Carton

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.5 cm
Package 1 Length	12 cm
Package 1 Weight	110 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations