

## Product data sheet

### Characteristics

# PDL56P440

## Plug - Straight, 40A, 500V, 4-Round Pin, Clear/Orange



### Main

Range	56 Series
Product or component type	Plug

### Complementary

Rated current	40 A
[Ue] rated operational voltage	500 V
Material	Plastic
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	4
Ambient air temperature for operation	-40...55 °C
Cable cross section	9...29 mm <sup>2</sup>
Quantity per set	Set of 4
Type of packing	Carton

### Environment

IP degree of protection	IP66
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.69 cm
Package 1 Width	7.64 cm
Package 1 Length	16.75 cm
Package 1 Weight	445.5 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations