

Product data sheet

Characteristics

PDL56P516QC

Plug - Straight, 16A, 500V, 5-Round Pin, Quick Connect Clear/Orange



Main

Range	56 Series
Product or component type	Plug

Complementary

Rated current	16 A
[Ue] rated operational voltage	500 V
Material	Plastic
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	5
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm ²
Quantity per set	Set of 4
Type of packing	Carton

Environment

IP degree of protection	IP66
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.27 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations