

# Product data sheet

## Characteristics

# PDL56PA416

Plug - Angled, 16A, 250V, 4-Round Pin, Clear/Orange



## Main

Range	56 Series
Product or component type	Plug

## Complementary

Rated current	16 A
[Ue] rated operational voltage	500 V
Material	Plastic
Colour tint	Orange
Surface finish	Gloss
Network frequency	50 Hz
Network number of phases	3 phases
Pin number	4
Ambient air temperature for operation	-40...55 °C
Cable cross section	7...16 mm <sup>2</sup>
Quantity per set	Set of 4
Type of packing	Carton

## Environment

IP degree of protection	IP66
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	18.0 cm
Package 1 Weight	280 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations